

Folding Handles, Revolving Ball Knobs

Similar Product Page: P.1151, 1152

Folding Handle

Type	Lever		Screw, Nut	
	M Material	M Material	M Material	S Surface Treatment
C-GRMBM	ABS	Carbon Steel for Mechanical Structure	Carbon Steel for Mechanical Structure	Black Oxide

⚠ The L Dim. Tolerance Range is ±2mm.
 ⚠ M8 Size product has no cap provided on the handle tip, while M10/M12 product has this cap provided there.
 ⚠ To fold the lever, pull up and fold down.
 ⚠ Folding angle is 90°.

Part Number		L	H	D	(h)	H ₁	W	Reference Mass (g)	Unit Price
Type	M								
C-GRMBM	8	15	87	23.5	18	91	13.5	71	
	10	19	95	26	20	96	14	129	
	12	24	95	26	21	97	16	136	

Ordering Example Part Number C-GRMBM8

Revolving Ball Knob

Type	Ball		Screw	
	M Material	M Material	M Material	S Surface Treatment
C-PBG	Phenol Resin	Carbon Steel for Mechanical Structure	Carbon Steel for Mechanical Structure	Zinc Plating

⚠ The L Dim. Tolerance Range is ±2mm.

Part Number		D	H	L	Lf	W	Reference Mass (g)	Unit Price
Type	M							
C-PBG	8	35	32	15	4	4	44	
	10	40	37	18	5	5	99	
	12	50	48	20	6	6	123	

Ordering Example Part Number C-PBG8

Cone Shaped Levers, Balance Handles

Similar Product Page: P.1148, 1153

Cone Shaped Lever

Type	Lever	
	M Material	S Surface Treatment
C-LRGNN	Carbon Steel for Mechanical Structure	Chrome Plating

⚠ P is H8 Hole.
 ⚠ The *d part is Dowel Pin Hole. For dowel pins, select the applicable product on P.255 or procure it separately from this catalog.

Part Number		L	D	H	B	d	Reference Mass (g)	Unit Price
Type	P							
C-LRGNN	5	40	12	9	7	2	15	
	6	50	14	10	8	2	19	
	8	63	16	11	10	3	33	
	10	80	20	14	12	3	66	
	12	100	25	18	15	4	134	
	16	125	32	22	18	5	229	

Ordering Example Part Number C-LRGNN5

Balanced Handle

Type	Body		Handle	
	M Material	M Material	M Material	S Surface Treatment
C-NOCH	Carbon Steel for Mechanical Structure	Chrome Plating	Carbon Steel for Mechanical Structure	Chrome Plating

⚠ P is H8 Hole.
 ⚠ The *d part is Dowel Pin Hole. For dowel pins, select the applicable product on P.255 or procure it separately from this catalog.

Part Number		A	K	H	D	d	h	B	Reference Mass (g)	Unit Price
Type	P									
C-NOCH	8	50	40	55	20	3	11	13	80	
	10	64	50	69	25	3	14	16	150	
	12	80	63	87	32	4	18	20	310	
	14	126	80	109	38	5	22	25	644	
	16	160	80	109	38	5	22	25	710	
	18	200	100	135	45	6	28	32	1300	

Ordering Example Part Number C-NOCH8