



FAG

★ 7212-B-XL-MP

Angular contact ball bearing

Schaeffler ID:
0191151720000Angular contact ball bearing 72..-B-XL-MP,
single row, X-life, solid brass cage

★ Preferred product

X-life

Technical information



Temperature range

T_{\min}	-30 °C	Operating temperature min.
T_{\max}	150 °C	Operating temperature max.
	0,88 kg	Weight

Main Dimensions & Performance Data

d	60 mm	Bore diameter
D	110 mm	Outside diameter
B	22 mm	Width
C_r	62.000 N	Basic dynamic load rating, radial
C_{0r}	45.000 N	Basic static load rating, radial
C_{ur}	3.150 N	Fatigue load limit, radial
n_G	10.800 1/min	Limiting speed
n_{gr}	6.200 1/min	Reference speed

Dimensions

r_{\min}	1,5 mm	Minimum chamfer dimension
$r_{1\min}$	1 mm	Minimum chamfer dimension
D_1	90,8 mm	Shoulder diameter on outer ring wide side face
d_1	80,32 mm	Shoulder diameter on inner ring wide side face
a	47 mm	Distance between the apexes of the pressure cones
α	40 °	Contact angle

Mounting dimensions

$d_{a\min}$	69 mm	Minimum diameter of shaft shoulder
$D_{a\max}$	101 mm	Maximum diameter of housing shoulder
$D_{b\max}$	104,4 mm	Maximaler Durchmesser der Gehäuseschulter
$r_{a\max}$	1,5 mm	Maximum fillet radius of shaft
$r_{a1\max}$	1 mm	Maximum fillet radius of housing

