



FAG

★ 7224-B-XL-MP

Angular contact ball bearing

Schaeffler ID:
0191161360000Angular contact ball bearing 72..-B-XL-MP,
single row, X-life, solid brass cage

★ Preferred product

X-life

Technical information



Temperature range

T_{min}	-30 °C	Operating temperature min.
T_{max}	150 °C	Operating temperature max.
	6,071 kg	Weight

Main Dimensions & Performance Data

d	120 mm	Bore diameter
D	215 mm	Outside diameter
B	40 mm	Width
C_r	182.000 N	Basic dynamic load rating, radial
C_{0r}	178.000 N	Basic static load rating, radial
C_{ur}	9.600 N	Fatigue load limit, radial
n_G	5.200 1/min	Limiting speed
n_{gr}	3.700 1/min	Reference speed

Dimensions

r_{min}	2,1 mm	Minimum chamfer dimension
$r_{1 min}$	1,1 mm	Minimum chamfer dimension
D_1	178,9 mm	Shoulder diameter on outer ring wide side face
d_1	157,2 mm	Shoulder diameter on inner ring wide side face
a	90 mm	Distance between the apexes of the pressure cones
α	40 °	Contact angle

Mounting dimensions

$d_{a min}$	132 mm	Minimum diameter of shaft shoulder
$D_{a max}$	203 mm	Maximum diameter of housing shoulder
$D_{b max}$	208 mm	Maximaler Durchmesser der Gehäuseschulter
$r_{a max}$	2,1 mm	Maximum fillet radius of shaft
$r_{a1 max}$	1 mm	Maximum fillet radius of housing

