



FAG

★ 7317-B-XL-MP


Angular contact ball bearing

Schaeffler ID:
0191179570000Angular contact ball bearing 73..-B-XL-MP,
single row, X-life, solid brass cage

★ Preferred product

X-life

Technical information



Temperature range

T_{min}	-30 °C	Operating temperature min.
T_{max}	150 °C	Operating temperature max.
	4,8 kg	Weight

Main Dimensions & Performance Data

d	85 mm	Bore diameter
D	180 mm	Outside diameter
B	41 mm	Width
C_r	167.000 N	Basic dynamic load rating, radial
C_{0r}	138.000 N	Basic static load rating, radial
C_{ur}	8.300 N	Fatigue load limit, radial
n_G	6.400 1/min	Limiting speed
n_{gr}	4.100 1/min	Reference speed

Dimensions

r_{min}	3 mm	Minimum chamfer dimension
r_{1min}	1,1 mm	Minimum chamfer dimension
D_1	144 mm	Shoulder diameter on outer ring wide side face
d_1	122 mm	Shoulder diameter on inner ring wide side face
a	76 mm	Distance between the apexes of the pressure cones
α	40 °	Contact angle

Mounting dimensions

d_{amin}	99 mm	Minimum diameter of shaft shoulder
D_{amax}	166 mm	Maximum diameter of housing shoulder
D_{bmax}	173 mm	Maximaler Durchmesser der Gehäuseschulter
r_{amax}	2,5 mm	Maximum fillet radius of shaft
r_{a1max}	1 mm	Maximum fillet radius of housing

