



FAG

★ 7412-B-XL-MP


Angular contact ball bearing

Schaeffler ID:
0191189370000Angular contact ball bearing 74..-B-XL-MP,
single row, X-life, solid brass cage

★ Preferred product

X-life

Technical information



Temperature range

T_{min}	-30 °C	Operating temperature min.
T_{max}	150 °C	Operating temperature max.
	3,14 kg	Weight

Main Dimensions & Performance Data

d	60 mm	Bore diameter
D	150 mm	Outside diameter
B	35 mm	Width
C_r	126.000 N	Basic dynamic load rating, radial
C_{0r}	93.000 N	Basic static load rating, radial
C_{ur}	6.200 N	Fatigue load limit, radial
n_G	7.800 1/min	Limiting speed
n_{gr}	3.950 1/min	Reference speed

Dimensions

r_{min}	2,1 mm	Minimum chamfer dimension
$r_{1 min}$	1,1 mm	Minimum chamfer dimension
D_1	119,6 mm	Shoulder diameter on outer ring wide side face
d_1	102,3 mm	Shoulder diameter on inner ring wide side face
a	62 mm	Distance between the apexes of the pressure cones
α	40 °	Contact angle

Mounting dimensions

$d_{a min}$	74 mm	Minimum diameter of shaft shoulder
$D_{a max}$	136 mm	Maximum diameter of housing shoulder
$D_{b max}$	141 mm	Maximaler Durchmesser der Gehäuseschulter
$r_{a max}$	2,1 mm	Maximum fillet radius of shaft
$r_{a1 max}$	1 mm	Maximum fillet radius of housing

