



FAG

★ 51207

Axial deep groove ball bearing

Schaeffler ID:
0167150470000Axial deep groove ball bearing 512, single
direction, steel sheet metal cage

★ Preferred product

Technical information



Temperature range

T_{\min}	-30 °C	Operating temperature min.
T_{\max}	150 °C	Operating temperature max.
	0,002 kg	Weight

Main Dimensions & Performance Data

d	35 mm	Bore diameter
D	62 mm	Outside diameter
T	18 mm	Height
C_a	35.500 N	Basic dynamic load rating, axial
C_{0a}	67.000 N	Basic static load rating, axial
C_{ua}	3.100 N	Fatigue load limit, axial
n_G	6.000 1/min	Limiting speed
n_{gr}	8.000 1/min	Reference speed

Dimensions

r_{\min}	1 mm	Minimum chamfer dimension
D_1	37 mm	Bore diameter housing washer
d_1	62 mm	Lip diameter shaft washer

Mounting dimensions

$d_{a \min}$	51 mm	Minimum diameter shaft shoulder
$D_{a \max}$	46 mm	Maximum diameter of housing shoulder
$r_{a \max}$	1 mm	Maximum recess radius

Additional information

A	0,028	Minimum load factor
---	-------	---------------------