

FAG



★ 51208

Axial deep groove ball bearing

Schaeffler ID:  
0167150550000Axial deep groove ball bearing 512, single  
direction, steel sheet metal cage

★ Preferred product

## Technical information



## Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	150 °C	Operating temperature max.
	0,268 kg	Weight

## Main Dimensions &amp; Performance Data

d	40 mm	Bore diameter
D	68 mm	Outside diameter
T	19 mm	Height
$C_a$	44.000 N	Basic dynamic load rating, axial
$C_{0a}$	97.000 N	Basic static load rating, axial
$C_{ua}$	4.400 N	Fatigue load limit, axial
$n_G$	5.500 1/min	Limiting speed
$n_{gr}$	6.900 1/min	Reference speed

## Dimensions

$r_{\min}$	1 mm	Minimum chamfer dimension
$D_1$	42 mm	Bore diameter housing washer
$d_1$	68 mm	Lip diameter shaft washer

## Mounting dimensions

$d_{a \min}$	57 mm	Minimum diameter shaft shoulder
$D_{a \max}$	51 mm	Maximum diameter of housing shoulder
$r_{a \max}$	1 mm	Maximum recess radius

## Additional information

A	0,05	Minimum load factor
---	------	---------------------