



FAG


★ 16026

Deep groove ball bearing

Schaeffler ID:
0167012910000Deep groove ball bearing 160, single row,
steel sheet metal cage

★ Preferred product

Technical information



Temperature range

T_{\min}	-30 °C	Operating temperature min.
T_{\max}	150 °C	Operating temperature max.
	2,41 kg	Weight

Main Dimensions & Performance Data

d	130 mm	Bore diameter
D	200 mm	Outside diameter
B	22 mm	Width
C_r	84.000 N	Basic dynamic load rating, radial
C_{0r}	82.000 N	Basic static load rating, radial
C_{ur}	3.750 N	Fatigue load limit, radial
n_G	4.650 1/min	Limiting speed
n_{gr}	3.450 1/min	Reference speed

Dimensions

r_{\min}	1,1 mm	Minimum chamfer dimension
D_1	176,7 mm	Shoulder diameter outer ring
d_1	154,7 mm	Shoulder diameter inner ring

Mounting dimensions

$d_{a\min}$	136 mm	Minimum diameter shaft shoulder
$D_{a\max}$	194 mm	Maximum diameter of housing shoulder
$r_{a\max}$	1 mm	Maximum fillet radius

Calculation factors

f_0	16,4	Calculation factor
-------	------	--------------------