



FAG


## ★ 6034

Deep groove ball bearing

Schaeffler ID:  
0167187040000Deep groove ball bearing 60, single row,  
steel sheet metal cage

★ Preferred product

## Technical information



## Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	200 °C	Operating temperature max.
	7,13 kg	Weight

## Main Dimensions &amp; Performance Data

d	170 mm	Bore diameter
D	260 mm	Outside diameter
B	42 mm	Width
$C_r$	179.000 N	Basic dynamic load rating, radial
$C_{0r}$	172.000 N	Basic static load rating, radial
$C_{ur}$	7.600 N	Fatigue load limit, radial
$n_G$	3.400 1/min	Limiting speed
$n_{gr}$	3.550 1/min	Reference speed

## Dimensions

$r_{\min}$	2,1 mm	Minimum chamfer dimension
$D_1$	231,2 mm	Shoulder diameter outer ring
$d_1$	199,4 mm	Shoulder diameter inner ring

## Mounting dimensions

$d_{a\min}$	180,2 mm	Minimum diameter shaft shoulder
$D_{a\max}$	249,8 mm	Maximum diameter of housing shoulder
$r_{a\max}$	2,1 mm	Maximum fillet radius

## Calculation factors

$f_0$	15,7	Calculation factor
-------	------	--------------------