



FAG

2209-2RS-TVH

Self-aligning ball bearing

Schaeffler ID:
0167028910000Self-aligning ball bearing 22..-2RS-TVH,
seals, plastic cage

Technical information

**Main Dimensions & Performance Data**

d	45 mm	Bore diameter
D	85 mm	Outside diameter
B	23 mm	Width
r_{\min}	1,1 mm	Minimum chamfer dimension
C_r	22.000 N	Basic dynamic load rating, radial
C_{0r}	7.300 N	Basic static load rating, radial
C_{ur}	465 N	Fatigue load limit, radial
n_G	4.650 1/min	Limiting speed
	0,527 kg	Weight

Dimensions

D_2	76 mm	Caliber diameter outer ring
d_2	53,8 mm	Caliber diameter inner ring

Mounting dimensions

$d_{a\min}$	52 mm	Minimum diameter shaft shoulder
$D_{a\max}$	78 mm	Maximum diameter of housing shoulder
$r_{a\max}$	1 mm	Maximum fillet radius

Calculation factors

e	0,21	Limiting value of F_a/F_r for the applicability of diff. Values of factors X and Y
Y_1	3,03	Dynamic axial load factor
Y_2	4,68	Dynamic axial load factor
Y_0	3,17	Static axial load factor

Temperature range

T_{\min}	-20 °C	Operating temperature min.
T_{\max}	100 °C	Operating temperature max.