



FAG

★ NJ307-E-XL-TVP2

Cylindrical roller bearing


Schaeffler ID:
0167361250000

★ Preferred product

Cylindrical roller bearing NJ..-E-XL-TVP2,
with cage, single row, semi-locating
bearing, 2 ribs on outer ring, 1 rib on inner
ring, type NJ

X-life

Technical information



Temperature range

T_{min}	-30 °C	Operating temperature min.
T_{max}	120 °C	Operating temperature max.
	0,481 kg	Weight

Main Dimensions & Performance Data

d	35 mm	Bore diameter
D	80 mm	Outside diameter
B	21 mm	Width
C_r	76.000 N	Basic dynamic load rating, radial
C_{0r}	63.000 N	Basic static load rating, radial
C_{ur}	10.800 N	Fatigue load limit, radial
n_G	10.900 1/min	Limiting speed
n_{gr}	7.900 1/min	Reference speed

Dimensions

r_{min}	1,5 mm	Minimum chamfer dimension
$r_{1 min}$	1,1 mm	Minimum chamfer dimension
s	0,6 mm	Axial displacement
E	70,2 mm	Raceway diameter outer ring
F	46,2 mm	Raceway diameter inner ring
$D_{1 min}$	66,6 mm	Minimum rib diameter outer ring
d_1	51 mm	Maximum rib diameter inner ring

Mounting dimensions

$d_{a min}$	42 mm	Minimum diameter shaft shoulder
$d_{a max}$	45 mm	Maximum diameter of shaft shoulder
$D_{a max}$	71 mm	Maximum diameter of housing shoulder
$d_{c min}$	53 mm	Minimum shaft shoulder
$r_{a max}$	1,5 mm	Maximum recess radius

Additional information

HJ307-E

L-washer

