

**NK38/30-XL**

Needle roller bearing

Schaeffler ID:
0507542700000

Needle roller bearings NK, light series

X-life

Technical information

**Main Dimensions & Performance Data**

F_w	38 mm	Under roller diameter
D	48 mm	Outside diameter
C	30 mm	Width, outer ring
C_r	43.000 N	Basic dynamic load rating, radial
C_{0r}	76.000 N	Basic static load rating, radial
C_{ur}	14.300 N	Fatigue load limit, radial
n_G	12.000 1/min	Limiting speed
n_{gr}	7.000 1/min	Reference speed
	0,001 kg	Weight

Additional information

r_{min}	0,3 mm	Minimum chamfer dimension
	G38X48X4	Sealing ring
	SD38X48X4	Sealing ring 2

Temperature range

T_{min}	-30 °C	Operating temperature min.
T_{max}	120 °C	Operating temperature max.