

RNAO16X28X12-XL




Needle roller bearing

Schaeffler ID:
0507758200000

Needle roller bearings RNAO, without ribs

X-life

Technical information



Main Dimensions & Performance Data

F_w	16 mm	Under roller diameter
D	28 mm	Outside diameter
C	12 mm	Width, outer ring
C_r	13.000 N	Basic dynamic load rating, radial
C_{0r}	12.500 N	Basic static load rating, radial
C_{ur}	2.250 N	Fatigue load limit, radial
n_G	22.900 1/min	Limiting speed
n_{gr}	15.900 1/min	Reference speed
	32 g	Weight

Dimensions

E	22 mm	Raceway diameter outer ring
r_{min}	0,3 mm	Minimum chamfer dimension

Mounting dimensions

D_b	16,4 mm	Shoulder diameter axial guidance NK/housing
d_b	21,6 mm	Shoulder diameter axial guidance NK/shaft
D_a	22,3 mm	Shoulder diameter outer ring
$r_{a max}$	0,3 mm	Maximum recess radius

Temperature range

T_{min}	-30 °C	Operating temperature min.
T_{max}	120 °C	Operating temperature max.