



## RALT25-XL

Flanged housing unit

Schaeffler ID:  
0008439460000

Flanged housing unit RALT..-XL

X-life

### Technical information

#### Main Dimensions & Performance Data

d	25 mm	Bore diameter
L	71 mm	Flange width
H	95,2 mm	Height flange
U	21,4 mm	Total height unit
C <sub>r</sub>	10.100 N	Basic dynamic load rating, radial
C <sub>0r</sub>	5.900 N	Basic static load rating, radial
C <sub>ur</sub>	280 N	Fatigue load limit, radial
C <sub>0rG</sub>	3.000 N	Load carrying capacity (housing)
C <sub>g</sub>	3.000 N	Load carrying capacity (housing)
	0,23 kg	Weight

#### Dimensions

A	7,1 mm	Height housing
	2	Number of housings
	FLAN47-LST	Housing
	RALE25-XL-NPP-B	Bearing designation
S	2 mm	Thickness of flange
V	55 mm	Shoulder diameter housing

#### Mounting dimensions

J	76 mm	Distance fixing bore
N	8,7 mm	Fixing square
n	2	Number of screwing holes