



## RTUEY80-XL


Take-up housing unit

Schaeffler ID:  
0009266800000

Take-up housing units RTUEY, cast iron housing, radial insert ball bearing with grub screws in inner ring, R seals

X-life

### Technical information



### Main Dimensions & Performance Data

d	80 mm	Bore diameter
H	184 mm	Height
L	230 mm	Length total
	7,46 kg	Weight

### Dimensions

L <sub>1</sub>	140 mm	Distance shaft axis
	TUE16	Housing
	GYE80-XL-KRR-B	Bearing designation
L <sub>2</sub>	20 mm	Length fixed link
L <sub>3</sub>	120 mm	Length guidance groove
A	70 mm	Width housing fixing side
N <sub>1</sub>	35 mm	Width recess
N <sub>2</sub>	70 mm	Height recess
T	110 mm	Height housing fixing side
Q	M6	Connection thread lubrication
A <sub>2</sub>	50 mm	Width housing

### Mounting dimensions

A <sub>1</sub>	28 mm	Width guidance groove
	H13	Width guidance groove clearance
H <sub>1</sub>	165 mm	Distance guidance grooves
	0,25 mm	Upper distance guidance groove tolerance
	-0,25 mm	Lower distance guidance groove tolerance
N	41 mm	Fixing bore

