


RSTO20

Yoke type track roller

Schaeffler ID:
0000542750000

Yoke type track rollers RSTO, without axial guidance, outer ring without ribs

Technical information



Main Dimensions & Performance Data

D	47 mm	Outside diameter
F_w	25 mm	Under roller diameter
C	15,8 mm	Width, outer ring
$C_{r w}$	16.100 N	Basic dynamic load rating, radial
$C_{0r w}$	22.000 N	Basic static load rating, radial
$C_{ur w}$	3.100 N	Fatigue load limit, radial
n_{DG}	2.400 1/min	Speed on permanent grease lubrication
	0,137 kg	Weight

Dimensions

E	32 mm	Raceway diameter outer ring
r_{min}	0,3 mm	Minimum chamfer dimension
R	500 mm	Radius of outer ring outside profile