


**FAG****7330-B-MP**

Angular contact ball bearing

Schaeffler ID:
0191185200000Angular contact ball bearing 73...-B-MP,
single row, solid brass cage

Technical information

**Main Dimensions & Performance Data**

d	150 mm	Bore diameter
D	320 mm	Outside diameter
B	65 mm	Width
C_r	340.000 N	Basic dynamic load rating, radial
C_{0r}	430.000 N	Basic static load rating, radial
C_{ur}	14.600 N	Fatigue load limit, radial
n_G	3.150 1/min	Limiting speed
n_{gr}	2.200 1/min	Reference speed
	25,478 kg	Weight

Additional information

r_{min}	4 mm	Minimum chamfer dimension
$r_{1 min}$	1,5 mm	Minimum chamfer dimension
D_1	255,8 mm	Shoulder diameter on outer ring wide side face
d_1	218,3 mm	Shoulder diameter on inner ring wide side face
a	131 mm	Distance between the apexes of the pressure cones
α	40 °	Contact angle

Mounting dimensions

$d_{a min}$	167 mm	Minimum diameter of shaft shoulder
$D_{a max}$	303 mm	Maximum diameter of housing shoulder
$D_{b max}$	311 mm	Maximaler Durchmesser der Gehäuseschulter
$r_{a max}$	3 mm	Maximum fillet radius of shaft
$r_{a1 max}$	1,5 mm	Maximum fillet radius of housing

Temperature range

T_{min}	-30 °C	Operating temperature min.
T_{max}	200 °C	Operating temperature max.

