





FAG

6226-2Z

Deep groove ball bearing

Schaeffler ID:
0191062700000Deep groove ball bearing 62...-2Z, single
row, shields, steel sheet metal cage

Technical information

**Main Dimensions & Performance Data**

d	130 mm	Bore diameter
D	230 mm	Outside diameter
B	40 mm	Width
C_r	177.000 N	Basic dynamic load rating, radial
C_{0r}	146.000 N	Basic static load rating, radial
C_{ur}	7.700 N	Fatigue load limit, radial
n_G	3.250 1/min	Limiting speed
n_{gr}	3.900 1/min	Reference speed
	6,14 kg	Weight

Dimensions

r_{min}	3 mm	Minimum chamfer dimension
D_2	203,5 mm	Caliber diameter outer ring
d_1	161 mm	Shoulder diameter inner ring

Mounting dimensions

$d_{a min}$	144 mm	Minimum diameter shaft shoulder
$D_{a max}$	216 mm	Maximum diameter of housing shoulder
$r_{a max}$	2,5 mm	Maximum fillet radius

Calculation factors

f_0	14,5	Calculation factor
-------	------	--------------------

Temperature range

T_{min}	-20 °C	Operating temperature min.
T_{max}	120 °C	Operating temperature max.