



FAG

**6321**

Deep groove ball bearing

Schaeffler ID:  
0167244450000Deep groove ball bearing 63, single row,  
steel sheet metal cage

## Technical information

**Main Dimensions & Performance Data**

d	105 mm	Bore diameter
D	225 mm	Outside diameter
B	49 mm	Width
$C_r$	188.000 N	Basic dynamic load rating, radial
$C_{0r}$	150.000 N	Basic static load rating, radial
$C_{ur}$	8.100 N	Fatigue load limit, radial
$n_G$	4.050 1/min	Limiting speed
$n_{gr}$	4.450 1/min	Reference speed
	8,7 kg	Weight

**Dimensions**

$r_{min}$	3 mm	Minimum chamfer dimension
$D_1$	187,9 mm	Shoulder diameter outer ring
$d_1$	144,3 mm	Shoulder diameter inner ring

**Mounting dimensions**

$d_{a min}$	119 mm	Minimum diameter shaft shoulder
$D_{a max}$	211 mm	Maximum diameter of housing shoulder
$r_{a max}$	2,5 mm	Maximum fillet radius

**Calculation factors**

$f_0$	13,7	Calculation factor
-------	------	--------------------

**Temperature range**

$T_{min}$	-30 °C	Operating temperature min.
$T_{max}$	150 °C	Operating temperature max.