

Shaft support blocks GWH25-B (Series GWH)

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue ordering system (https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp) or by telephone on +49 (91 32) 82 - 28 97.

D	25 mm	Tolerance: H8
H	52,5 mm	
B	60 mm	
L	28 mm	
A5	30 mm	
B1	44 mm	
G2	M10	
H2	31 mm	Tolerance: +0,01/-0,01
H4	36,6 mm	
H5	9,9 mm	
H6	26 mm	
JB	44 mm	Tolerance: +0,15/-0,15
K5	M8	for fixing screws to ISO 4762-8.8 If there is a possibility of settling, the screws should be secured

	against rotation.	
N ₁	8,4 mm	
N ₃	18 mm	
T ₅	22 mm	
W	5 mm	Width across flats
m	0,17 kg	Mass of shaft support block



