

## Shaft support blocks GWN50-B (Series GWN)

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue ordering system ([https://www.schaeffler.de/content.schaeffler.de/en/news\\_media/index.jsp](https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp)) or by telephone on +49 (91 32) 82 - 28 97.

D	50 mm	Tolerance: H8
H	105 mm	
B	132 mm	
L	58 mm	
A5	66 mm	Tolerance: +0,01/-0,01
B1	90 mm	
G2	M20	
H2	60 mm	Tolerance: +0,01/-0,01
H4	62 mm	
H5	10,6 mm	
H6	49 mm	
JB	100 mm	Tolerance: +0,2/-0,2
JB1	70 mm	

JL	36 mm	
K5	M16	for fixing screws to ISO 4762-8.8 If there is a possibility of settling, the screws should be secured against rotation.
N1	17,5 mm	
N3	26 mm	
N4	12 mm	Centring for dowel hole
T5	43 mm	
W	10 mm	
m	1,4 kg	Mass of shaft support block



