

Shaft support blocks GWN40-B (Series GWN)

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue ordering system (https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp) or by telephone on +49 (91 32) 82 - 28 97.

D	40 mm	Tolerance: H8
H	90 mm	
B	108 mm	
L	48 mm	
A5	54 mm	Tolerance: +0,01/-0,01
B1	76 mm	
G2	M16	
H2	50 mm	Tolerance: +0,01/-0,01
H4	57,6 mm	
H5	11,7 mm	
H6	44 mm	
JB	82 mm	Tolerance: +0,15/-0,15
JB1	65 mm	

JL	32 mm	
K5	M12	for fixing screws to ISO 4762-8.8 If there is a possibility of settling, the screws should be secured against rotation.
N1	13,5 mm	
N3	20 mm	
N4	10 mm	Centring for dowel hole
T5	34 mm	
W	8 mm	
m	0,85 kg	Mass of shaft support block



