

Shaft support blocks GWN12-B (Series GWN)

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue ordering system (https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp) or by telephone on +49 (91 32) 82 - 28 97.

D	12 mm	Tolerance: H8
H	35 mm	
B	43 mm	
L	20 mm	
A5	21,5 mm	Tolerance: +0,01/-0,01
B1	34 mm	
G2	M6	
H2	20 mm	Tolerance: +0,01/-0,01
H4	26,6 mm	
H5	5,4 mm	
H6	16,5 mm	
JB	30 mm	Tolerance: +0,15/-0,15
JB1	20 mm	

JL	13 mm	
K5	M5	for fixing screws to ISO 4762-8.8 If there is a possibility of settling, the screws should be secured against rotation.
N1	5,3 mm	
N3	10 mm	
N4	4 mm	Centring for dowel hole
T5	13 mm	
W	3 mm	
m	0,06 kg	Mass of shaft support block



