

## Linear plain bearings PAB16-PP-AS (Series PAB..-PP-AS)

sealed on all sides, with relubrication facility

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue ordering system ([https://www.schaeffler.de/content.schaeffler.de/en/news\\_media/index.jsp](https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp)) or by telephone on +49 (91 32) 82 - 28 97.

F <sub>w</sub>	16 mm	
D	26 mm	Tolerance: h7
L	36 mm	Tolerance: h12
Bl <sub>2</sub>	1,3 mm	Tolerance: H13 Slot dimensions suitable for retaining rings to DIN 471.
D <sub>N</sub>	24,9 mm	
L <sub>2</sub>	24,6 mm	Tolerance: H13 Holes symmetrical to bearing length L.
NL	2,5 mm	Tolerance: H13
m	34 g	Mass of bearing
C <sub>0</sub>	96000 N	The basic static load ratings stated here are no longer valid if the bearings are mounted in housings.

