

Linear plain bearing and housing units

PAGBA30-PP-AS (Series PAGBA..-PP-AS)

sealed on all sides, with relubrication facility

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue ordering system (https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp) or by telephone on +49 (91 32) 82 - 28 97.

F _w	30 mm	
H	67 mm	
B	84 mm	
L	68 mm	Tolerance: h12
A ₃	25 mm	
A ₅	42 mm	Tolerance: +0,01/-0,01
H ₂	35 mm	Tolerance: +0,01/-0,01
H ₆	8,7 mm	Tolerance: 0/-0,5
J _B	68 mm	Tolerance: +0,2/-0,2
J _L	45 mm	Tolerance: +0,2/-0,2
K ₅	M6	
K ₈	NIPA2	Lubrication nipple

