

## Linear plain bearing and housing units

### PAGBAO50-PP-AS (Series PAGBAO..-PP-AS)

open design, sealed on all sides, with relubrication facility

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue ordering system ([https://www.schaeffler.de/content.schaeffler.de/en/news\\_media/index.jsp](https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp)) or by telephone on +49 (91 32) 82 - 28 97.

Fw	50 mm	
H	92,8 mm	
B	130 mm	
L	100 mm	Tolerance: h12
A3	19 mm	
A5	65 mm	
B2	22,7 mm	Dimension B2 on diameter Fw
H2	50 mm	
H6	12,5 mm	Tolerance: 0/-0,5
JB	108 mm	Tolerance: +0,2/-0,2
JL	50 mm	Tolerance: +0,2/-0,2
K5	M8	

K8	NIPA2	Lubrication nipple
L4	70 mm	
L5	72 mm	
N1	9,2 mm	for fixing screws to ISO 4762-8.8 If there is a possibility of settling, the screws should be secured against rotation.
N3	15 mm	for fixing screws to ISO 4762-8.8 If there is a possibility of settling, the screws should be secured against rotation.
W	4 mm	Note maximum tightening torque. Tightening torque max. 7 Nm
$\alpha$	54 °	
m	1,46 kg	Mass

