

## Linear plain bearings PABO50-PP-AS (Series PABO..-PP-AS)

open design, sealed on all sides, with relubrication facility

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue ordering system ([https://www.schaeffler.de/content.schaeffler.de/en/news\\_media/index.jsp](https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp)) or by telephone on +49 (91 32) 82 - 28 97.

Fw	50 mm	
D	75 mm	
L	100 mm	Tolerance: h12
B2	22,7 mm	Dimension B2 on diameter Fw
BL2	2,65 mm	Tolerance: H13 Slot dimensions suitable for retaining rings to DIN 471.
DN	72 mm	
L2	77,3 mm	Tolerance: H13 Holes symmetrical to bearing length L.
N4	3 mm	
NL	4 mm	Tolerance: H13
T4	1,5 mm	
$\alpha$	54 °	

m	657 g	Mass of bearing
C <sub>0</sub>	1000000 N	The basic static load ratings stated here are no longer valid if the bearings are mounted in housings.



