

## Linear plain bearing and housing units

### PAGBA12-PP-AS (Series PAGBA..-PP-AS)

sealed on all sides, with relubrication facility

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue ordering system ([https://www.schaeffler.de/content.schaeffler.de/en/news\\_media/index.jsp](https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp)) or by telephone on +49 (91 32) 82 - 28 97.

F <sub>w</sub>	12 mm	
H	34 mm	
B	42 mm	
L	32 mm	Tolerance: h12
A <sub>3</sub>	15 mm	
A <sub>5</sub>	21 mm	Tolerance: +0,01/-0,01
H <sub>2</sub>	18 mm	Tolerance: +0,01/-0,01
H <sub>6</sub>	4,8 mm	Tolerance: 0/-0,5
J <sub>B</sub>	32 mm	Tolerance: +0,15/-0,15
J <sub>L</sub>	23 mm	Tolerance: +0,15/-0,15
K <sub>5</sub>	M4	
K <sub>8</sub>	NIPA1	Lubrication nipple

L4	32 mm	
L5	20 mm	
N1	4,7 mm	for fixing screws to ISO 4762-8.8 If there is a possibility of settling, the screws should be secured against rotation.
N3	8 mm	for fixing screws to ISO 4762-8.8 If there is a possibility of settling, the screws should be secured against rotation.
m	0,07 kg	Mass



