



FAG



★ 6010

Deep groove ball bearing

Schaeffler ID:
0167176600000Deep groove ball bearing 60, single row,
steel sheet metal cage

★ Preferred product

Technical information



Temperature range

T_{\min}	-30 °C	Operating temperature min.
T_{\max}	120 °C	Operating temperature max.
	0,258 kg	Weight

Main Dimensions & Performance Data

d	50 mm	Bore diameter
D	80 mm	Outside diameter
B	16 mm	Width
C_r	22.000 N	Basic dynamic load rating, radial
C_{0r}	15.800 N	Basic static load rating, radial
C_{ur}	800 N	Fatigue load limit, radial
n_G	12.200 1/min	Limiting speed
n_{gr}	8.900 1/min	Reference speed

Dimensions

r_{\min}	1 mm	Minimum chamfer dimension
D_1	70,1 mm	Shoulder diameter outer ring
d_1	59,8 mm	Shoulder diameter inner ring

Mounting dimensions

$d_{a\min}$	54,6 mm	Minimum diameter shaft shoulder
$D_{a\max}$	75,4 mm	Maximum diameter of housing shoulder
$r_{a\max}$	1 mm	Maximum fillet radius

Calculation factors

f_0	15,6	Calculation factor
-------	------	--------------------