

**FAG**★ **ARCANOL-LOAD1000-5KG**

Sales grease

Schaeffler ID:  
0190034630000

ARCANOL-LOAD1000

★ Preferred product

## Technical information

**Technical data**

$\vartheta_{O_{min}}$	-20 °C	Operating temperature, min.
$\vartheta_{O_{max}}$	130 °C	Operating temperature, max.
$\vartheta_G$	80 °C	Upper continuous limit temperature
$n \cdot d_M$	300.000 mm/min	Speed of rotation specific value
	Lithium/calcium soap	Thickener type
	Mineral oil	Base oil type
$\nu_{40}$	1.000 mm <sup>2</sup> /s	Base oil viscosity at +40°C
$\nu_{100}$	38 mm <sup>2</sup> /s	Base oil viscosity at +100 °C
	2	NLGI class
	Heavy-duty grease	Grease category
$\rho$	0,93 kg/dm <sup>3</sup>	Density
	5 kg bucket	Container
	5 kg	Weight