

**FAG****ARCANOL-LOAD220-1KG**

Sales grease

Schaeffler ID:  
0386520990000

ARCANOL-LOAD220

## Technical information

**Technical data**

$\vartheta_{O_{min}}$	-20 °C	Operating temperature, min.
$\vartheta_{O_{max}}$	140 °C	Operating temperature, max.
$\vartheta_G$	80 °C	Upper continuous limit temperature
$n \cdot d_M$	500.000 mm/min	Speed of rotation specific value
	Lithium complex soap	Thickener type
	Mineral oil	Base oil type
$v_{40}$	245 mm <sup>2</sup> /s	Base oil viscosity at +40°C
$v_{100}$	20 mm <sup>2</sup> /s	Base oil viscosity at +100 °C
	2	NLGI class
	Heavy-duty grease	Grease category
$\rho$	0,9 kg/dm <sup>3</sup>	Density
	1 kg can	Container
	1 kg	Weight