

**FAG**★ **ARCANOL-LOAD400-1KG**

Sales grease

Schaeffler ID:
0386521020000

ARCANOL-LOAD400

★ Preferred product

Technical information

Technical data

$\vartheta_{O_{min}}$	-40 °C	Operating temperature, min.
$\vartheta_{O_{max}}$	130 °C	Operating temperature, max.
ϑ_G	80 °C	Upper continuous limit temperature
$n \cdot d_M$	400.000 mm/min	Speed of rotation specific value
	Lithium complex soap	Thickener type
	Mineral oil	Base oil type
v_{40}	400 mm ² /s	Base oil viscosity at +40°C
v_{100}	27 mm ² /s	Base oil viscosity at +100 °C
	2	NLGI class
	Heavy-duty grease	Grease category
ρ	0,9 kg/dm ³	Density
	1 kg can	Container
	1,055 kg	Weight