

**FAG**★ **ARCANOL-LOAD400-400G**

Sales grease

Schaeffler ID:  
0191438180000

ARCANOL-LOAD400

★ Preferred product

## Technical information

**Technical data**

|                       |                        |                                    |
|-----------------------|------------------------|------------------------------------|
| $\vartheta_{O_{min}}$ | -40 °C                 | Operating temperature, min.        |
| $\vartheta_{O_{max}}$ | 130 °C                 | Operating temperature, max.        |
| $\vartheta_G$         | 80 °C                  | Upper continuous limit temperature |
| $n \cdot d_M$         | 400.000 mm/min         | Speed of rotation specific value   |
|                       | Lithium complex soap   | Thickener type                     |
|                       | Mineral oil            | Base oil type                      |
| $v_{40}$              | 400 mm <sup>2</sup> /s | Base oil viscosity at +40°C        |
| $v_{100}$             | 27 mm <sup>2</sup> /s  | Base oil viscosity at +100 °C      |
|                       | 2                      | NLGI class                         |
|                       | Heavy-duty grease      | Grease category                    |
| $\rho$                | 0,9 kg/dm <sup>3</sup> | Density                            |
|                       | 400 g cartridge        | Container                          |
|                       | 0,005 kg               | Weight                             |