

**FAG**★ **ARCANOL-MULTI2-1KG**

Sales grease

Schaeffler ID:
0386521290000

ARCANOL-MULTI2

★ Preferred product

Technical information

Technical data

$\vartheta_{O_{min}}$	-30 °C	Operating temperature, min.
$\vartheta_{O_{max}}$	120 °C	Operating temperature, max.
ϑ_G	75 °C	Upper continuous limit temperature
$n \cdot d_M$	500.000 mm/min	Speed of rotation specific value
	Lithium soap	Thickener type
	Mineral oil	Base oil type
v_{40}	110 mm ² /s	Base oil viscosity at +40°C
v_{100}	11 mm ² /s	Base oil viscosity at +100 °C
	2	NLGI class
	Multi-purpose grease	Grease category
ρ	0,95 kg/dm ³	Density
	1 kg can	Container
	1,064 kg	Weight