

**FAG**★ **ARCANOL-MULTI2-250G**

Sales grease

Schaeffler ID:  
0190034710000

ARCANOL-MULTI2

★ Preferred product

## Technical information

**Technical data**

$\vartheta_{O_{min}}$	-30 °C	Operating temperature, min.
$\vartheta_{O_{max}}$	120 °C	Operating temperature, max.
$\vartheta_G$	75 °C	Upper continuous limit temperature
$n \cdot d_M$	500.000 mm/min	Speed of rotation specific value
	Lithium soap	Thickener type
	Mineral oil	Base oil type
$v_{40}$	110 mm <sup>2</sup> /s	Base oil viscosity at +40°C
$v_{100}$	11 mm <sup>2</sup> /s	Base oil viscosity at +100 °C
	2	NLGI class
	Multi-purpose grease	Grease category
$\rho$	0,95 kg/dm <sup>3</sup>	Density
	250 g tube	Container
	0,28 kg	Weight