

**FAG**★ **ARCANOL-MULTITOP-250G**

Sales grease

Schaeffler ID:
0191439900000

ARCANOL-MULTITOP

★ Preferred product

Technical information

Technical data

$\vartheta_{O_{min}}$	-50 °C	Operating temperature, min.
$\vartheta_{O_{max}}$	140 °C	Operating temperature, max.
ϑ_G	80 °C	Upper continuous limit temperature
$n \cdot d_M$	800.000 mm/min	Speed of rotation specific value
	Lithium soap	Thickener type
	Partially synthetic oil	Base oil type
v_{40}	82 mm ² /s	Base oil viscosity at +40°C
v_{100}	12,5 mm ² /s	Base oil viscosity at +100 °C
	2	NLGI class
	Multi-purpose grease	Grease category
ρ	0,87 kg/dm ³	Density
	250 g tube	Container
	0,28 kg	Weight