

**FAG**★ **ARCANOL-MULTITOP-5KG**

Sales grease

Schaeffler ID:  
0386521700000

ARCANOL-MULTITOP

★ Preferred product

## Technical information

**Technical data**

$\vartheta_{O_{min}}$	-50 °C	Operating temperature, min.
$\vartheta_{O_{max}}$	140 °C	Operating temperature, max.
$\vartheta_G$	80 °C	Upper continuous limit temperature
$n \cdot d_M$	800.000 mm/min	Speed of rotation specific value
	Lithium soap	Thickener type
	Partially synthetic oil	Base oil type
$v_{40}$	82 mm <sup>2</sup> /s	Base oil viscosity at +40°C
$v_{100}$	12,5 mm <sup>2</sup> /s	Base oil viscosity at +100 °C
	2	NLGI class
	Multi-purpose grease	Grease category
$\rho$	0,87 kg/dm <sup>3</sup>	Density
	5 kg bucket	Container
	5,527 kg	Weight