

**FAG**★ **ARCANOL-SPEED2,6-1KG**

Sales grease

Schaeffler ID:
0191440320000

ARCANOL-SPEED2,6

★ Preferred product

Technical information

Technical data

$\vartheta_{O_{min}}$	-40 °C	Operating temperature, min.
$\vartheta_{O_{max}}$	120 °C	Operating temperature, max.
ϑ_G	80 °C	Upper continuous limit temperature
$n \cdot d_M$	2.000.000 mm/min	Speed of rotation specific value
	Lithium complex soap	Thickener type
	Synthetic oil	Base oil type
ν_{40}	25 mm ² /s	Base oil viscosity at +40°C
ν_{100}	6 mm ² /s	Base oil viscosity at +100 °C
	2/3	NLGI class
	Special grease	Grease category
ρ	0,94 kg/dm ³	Density
	1 kg can	Container
	1 kg	Weight