

**FAG**★ **ARCANOL-TEMP110-400G**

Sales grease

Schaeffler ID:
0191440750000

ARCANOL-TEMP110

★ Preferred product

Technical information

Technical data

$\vartheta_{O_{min}}$	-35 °C	Operating temperature, min.
$\vartheta_{O_{max}}$	160 °C	Operating temperature, max.
ϑ_G	110 °C	Upper continuous limit temperature
$n \cdot d_M$	500.000 mm/min	Speed of rotation specific value
	Lithium complex soap	Thickener type
	Partially synthetic oil	Base oil type
v_{40}	130 mm ² /s	Base oil viscosity at +40°C
v_{100}	14 mm ² /s	Base oil viscosity at +100 °C
	2	NLGI class
	High-temperature grease	Grease category
ρ	0,9 kg/dm ³	Density
	400 g cartridge	Container
	0,45 kg	Weight