

**FAG**★ **ARCANOL-TEMP90-1KG**

Sales grease

Schaeffler ID:
0386521880000

ARCANOL-TEMP90

★ Preferred product

Technical information

Technical data

$\vartheta_{O_{min}}$	-40 °C	Operating temperature, min.
$\vartheta_{O_{max}}$	160 °C	Operating temperature, max.
ϑ_G	90 °C	Upper continuous limit temperature
$n \cdot d_M$	700.000 mm/min	Speed of rotation specific value
	Polycarbamide	Thickener type
	Mineral oil	Base oil type
v_{40}	148 mm ² /s	Base oil viscosity at +40°C
v_{100}	15,5 mm ² /s	Base oil viscosity at +100 °C
	3	NLGI class
	High-temperature grease	Grease category
ρ	0,9 kg/dm ³	Density
	1 kg can	Container
	1 kg	Weight