

**FAG**★ **ARCANOL-VIB3-5KG**

Sales grease

Schaeffler ID:  
0191442100000

ARCANOL-VIB3

★ Preferred product

## Technical information

**Technical data**

$\vartheta_{O_{min}}$	-30 °C	Operating temperature, min.
$\vartheta_{O_{max}}$	150 °C	Operating temperature, max.
$\vartheta_G$	90 °C	Upper continuous limit temperature
$n \cdot d_M$	350.000 mm/min	Speed of rotation specific value
	Lithium complex soap	Thickener type
	Mineral oil	Base oil type
$v_{40}$	170 mm <sup>2</sup> /s	Base oil viscosity at +40°C
$v_{100}$	14 mm <sup>2</sup> /s	Base oil viscosity at +100 °C
	3	NLGI class
	Special grease	Grease category
$\rho$	0,9 kg/dm <sup>3</sup>	Density
	5 kg bucket	Container
	5 kg	Weight