

**FAG**★ **ARCANOL-LOAD1000-25KG**

Sales grease

Schaeffler ID:
0191437290000

ARCANOL-LOAD1000

★ Preferred product

Technical information

Technical data

$\vartheta_{O_{min}}$	-20 °C	Operating temperature, min.
$\vartheta_{O_{max}}$	130 °C	Operating temperature, max.
ϑ_G	80 °C	Upper continuous limit temperature
$n \cdot d_M$	300.000 mm/min	Speed of rotation specific value
	Lithium/calcium soap	Thickener type
	Mineral oil	Base oil type
ν_{40}	1.000 mm ² /s	Base oil viscosity at +40°C
ν_{100}	38 mm ² /s	Base oil viscosity at +100 °C
	2	NLGI class
	Heavy-duty grease	Grease category
ρ	0,93 kg/dm ³	Density
	25 kg hobbock	Container
	25 kg	Weight