

**FAG**★ **ARCANOL-LOAD460-180KG**

Sales grease

Schaeffler ID:  
0658271800000

ARCANOL-LOAD460

★ Preferred product

## Technical information

**Technical data**

$\vartheta_{O_{min}}$	-40 °C	Operating temperature, min.
$\vartheta_{O_{max}}$	130 °C	Operating temperature, max.
$\vartheta_G$	80 °C	Upper continuous limit temperature
$n \cdot d_M$	400.000 mm/min	Speed of rotation specific value
	Lithium/calcium soap	Thickener type
	Mineral oil	Base oil type
$v_{40}$	400 mm <sup>2</sup> /s	Base oil viscosity at +40°C
$v_{100}$	25,8 mm <sup>2</sup> /s	Base oil viscosity at +100 °C
	1	NLGI class
	Heavy-duty grease	Grease category
$\rho$	0,93 kg/dm <sup>3</sup>	Density
	180 kg drum	Container
	180 kg	Weight