

**FAG****ARCANOL-CLEAN-M-250G**

Sales grease

Schaeffler ID:  
0694286110000

ARCANOL-CLEAN-M

## Technical information

**Technical data**

$\vartheta_{O_{min}}$	-30 °C	Operating temperature, min.
$\vartheta_{O_{max}}$	180 °C	Operating temperature, max.
$\vartheta_G$	90 °C	Upper continuous limit temperature
$n \cdot d_M$	850.000 mm/min	Speed of rotation specific value
	Polycarbamide	Thickener type
	Ether oil	Base oil type
$v_{40}$	103 mm <sup>2</sup> /s	Base oil viscosity at +40°C
$v_{100}$	12,8 mm <sup>2</sup> /s	Base oil viscosity at +100 °C
	2	NLGI class
	Special grease	Grease category
$\rho$	0,95 kg/dm <sup>3</sup>	Density
	250 g tube	Container
	0,25 kg	Weight