

**FAG****ARCANOL-MOTION2-1KG**

Sales grease

Schaeffler ID:  
0802663390000

ARCANOL-MOTION2

## Technical information

**Technical data**

$\vartheta_{O_{min}}$	-40 °C	Operating temperature, min.
$\vartheta_{O_{max}}$	130 °C	Operating temperature, max.
$\vartheta_G$	75 °C	Upper continuous limit temperature
$n \cdot d_M$	500.000 mm/min	Speed of rotation specific value
	Lithium soap	Thickener type
	Synthetic oil	Base oil type
$v_{40}$	50 mm <sup>2</sup> /s	Base oil viscosity at +40°C
$v_{100}$	8 mm <sup>2</sup> /s	Base oil viscosity at +100 °C
	2	NLGI class
	Special grease	Grease category
$\rho$	0,91 kg/dm <sup>3</sup>	Density
	1 kg can	Container
	1 kg	Weight