

**FAG****ARCANOL-MOTION2-25KG**

Sales grease

Schaeffler ID:
0802670090000

ARCANOL-MOTION2

Technical information

Technical data

$\vartheta_{O_{min}}$	-40 °C	Operating temperature, min.
$\vartheta_{O_{max}}$	130 °C	Operating temperature, max.
ϑ_G	75 °C	Upper continuous limit temperature
$n \cdot d_M$	500.000 mm/min	Speed of rotation specific value
	Lithium soap	Thickener type
	Synthetic oil	Base oil type
v_{40}	50 mm ² /s	Base oil viscosity at +40°C
v_{100}	8 mm ² /s	Base oil viscosity at +100 °C
	2	NLGI class
	Special grease	Grease category
ρ	0,91 kg/dm ³	Density
	25 kg hobbock	Container
	25 kg	Weight