



★ NK19/16-XL

Needle roller bearing

Schaeffler ID:
0507535330000

Needle roller bearings NK, light series

★ Preferred product

X-life

Technical information



Temperature range

T_{\min}	-30 °C	Operating temperature min.
T_{\max}	120 °C	Operating temperature max.
	26,76 g	Weight

Main Dimensions & Performance Data

F_w	19 mm	Under roller diameter
D	27 mm	Outside diameter
C	16 mm	Width, outer ring
C_r	14.700 N	Basic dynamic load rating, radial
C_{0r}	17.400 N	Basic static load rating, radial
C_{ur}	3.250 N	Fatigue load limit, radial
n_G	21.600 1/min	Limiting speed
n_{gr}	13.700 1/min	Reference speed

Dimensions

r_{\min}	0,3 mm	Minimum chamfer dimension
------------	--------	---------------------------

Additional information

G19X27X4	Sealing ring
SD19X27X4	Sealing ring 2