



★ NK21/20-XL

Needle roller bearing

Schaeffler ID:
0507537380000

Needle roller bearings NK, light series

★ Preferred product

X-life

Technical information



Temperature range

T_{\min}	-30 °C	Operating temperature min.
T_{\max}	120 °C	Operating temperature max.
	35,7 g	Weight

Main Dimensions & Performance Data

F_w	21 mm	Under roller diameter
D	29 mm	Outside diameter
C	20 mm	Width, outer ring
C_r	19.300 N	Basic dynamic load rating, radial
C_{0r}	25.500 N	Basic static load rating, radial
C_{ur}	4.500 N	Fatigue load limit, radial
n_G	20.600 1/min	Limiting speed
n_{gr}	12.300 1/min	Reference speed

Dimensions

r_{\min}	0,3 mm	Minimum chamfer dimension
------------	--------	---------------------------

Additional information

	G21X29X4	Sealing ring
--	----------	--------------