



## ★ NK26/16-XL

Needle roller bearing

Schaeffler ID:  
0507541060000

Needle roller bearings NK, light series

★ Preferred product

X-life

### Technical information



#### Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	120 °C	Operating temperature max.
	34,2 g	Weight

#### Main Dimensions & Performance Data

$F_w$	26 mm	Under roller diameter
$D$	34 mm	Outside diameter
$C$	16 mm	Width, outer ring
$C_r$	17.300 N	Basic dynamic load rating, radial
$C_{0r}$	23.600 N	Basic static load rating, radial
$C_{ur}$	4.450 N	Fatigue load limit, radial
$n_G$	17.200 1/min	Limiting speed
$n_{gr}$	10.300 1/min	Reference speed

#### Dimensions

$r_{\min}$	0,3 mm	Minimum chamfer dimension
------------	--------	---------------------------

#### Additional information

G26X34X4	Sealing ring
SD26X34X4	Sealing ring 2