



★ NK30/20-TV-XL

Needle roller bearing

Schaeffler ID:
0507541730000

Needle roller bearings NK, light series

★ Preferred product

X-life

Technical information



Temperature range

T_{\min}	-20 °C	Operating temperature min.
T_{\max}	120 °C	Operating temperature max.
	63,85 g	Weight

Main Dimensions & Performance Data

F_w	30 mm	Under roller diameter
D	40 mm	Outside diameter
C	20 mm	Width, outer ring
C_r	28.000 N	Basic dynamic load rating, radial
C_{0r}	41.000 N	Basic static load rating, radial
C_{ur}	7.300 N	Fatigue load limit, radial
n_G	14.800 1/min	Limiting speed
n_{gr}	8.500 1/min	Reference speed

Dimensions

r_{\min}	0,3 mm	Minimum chamfer dimension
------------	--------	---------------------------

Additional information

G30X40X4	Sealing ring
SD30X40X4	Sealing ring 2